

Network Camera Firmware Version: V5.5.113 Release Note (2021-03-19)

Firmware		
Basic Information	Firmware Version:	V5.5.113 build210317

2xx3G2, 2xx6G2, 2xx7G2, 3xx6G2, 3xx7G2 Camera V5.5.113 Features

1. New Features

• Newly release 52 models, please refer to the list of supported models for specific models.

Customer Impact and Recommended Action

This update refers to function/compatibility improvement and will take effect automatically after the Date of Change. We are very sorry for any inconvenience of use-habit changes caused by this action. For any questions and request for this firmware, please contact our local technical support team.

Remarks:

- Hikvision reserves the right to change, alter or withdraw the above notification without prior notice.
- Product design and specifications are subject to change without prior notice.
- The Hikvision firmware may contain errors known as errata which may cause the product to deviate from published specifications. Current characterized errata are available on request.
- Hikvision is not liable for any typing or printing errors.

Hikvision Digital Technology CO., Ltd.

No. 555 Qianmo Road, Binjiang District, Hangzhou 310051, China

Tel: +86-571-8807-5998



Supported Product List (1x83G0, 2xx3G2, 2xx6G2(C), 2xx7G2(C), 3xx6G2(C), 3xx7G2(C) Series)

2xx/G2(C), 3xx6G2(C), 3xx/G2(C) Series)				
Product Category	Model Number			
1 Series	DS-2CD1083G0-I(U)(F)			
1 Series	DS-2CD1183G0-I(U)(F)			
1 Series	DS-2CD1383G0-I(U)(F)			
Pro Series	DS-2CD2023G2-I(U)			
Pro Series	DS-2CD2043G2-I(U)			
Pro Series	DS-2CD2063G2-I(U)			
Pro Series	DS-2CD2083G2-I(U)			
Pro Series	DS-2CD2123G2-I(S)			
Pro Series	DS-2CD2123G2-IU			
Pro Series	DS-2CD2143G2-I(S)			
Pro Series	DS-2CD2143G2-IU			
Pro Series	DS-2CD2163G2-I(S)			
Pro Series	DS-2CD2163G2-IU			
Pro Series	DS-2CD2183G2-I(S)			
Pro Series	DS-2CD2183G2-IU			
Pro Series	DS-2CD2323G2-I(U)			
Pro Series	DS-2CD2343G2-I(U)			
Pro Series	DS-2CD2363G2-I(U)			
Pro Series	DS-2CD2383G2-I(U)			
Pro Series	DS-2CD2423G2-I			
Pro Series	DS-2CD2443G2-I			
Pro Series	DS-2CD2463G2-I			
Pro Series	DS-2CD2483G2-I			
Pro Series	DS-2CD2623G2-IZS			
Pro Series	DS-2CD2643G2-IZS			



DS-2CD2663G2-IZS
DS-2CD2683G2-IZS
DS-2CD2723G2-IZS
DS-2CD2743G2-IZS
DS-2CD2763G2-IZS
DS-2CD2783G2-IZS
DS-2CD2H23G2-IZS
DS-2CD2H43G2-IZS
DS-2CD2H63G2-IZS
DS-2CD2H83G2-IZS
DS-2CD2T23G2-2I/4I
DS-2CD2T43G2-2I/4I
DS-2CD2T63G2-2I/4I
DS-2CD2T83G2-2I/4I
DS-2CD2026G2-I(U)(C)
DS-2CD2026G2-IU/SL(C)
DS-2CD2046G2-I(U)(C)
DS-2CD2046G2-IU/SL(C)
DS-2CD2066G2-I(U)(C)
DS-2CD2066G2-IU/SL(C)
DS-2CD2086G2-I(U)(C)
DS-2CD2126G2-I(SU)(C)
DS-2CD2146G2-I(SU)(C)
DS-2CD2166G2-I(SU)(C)
DS-2CD2186G2-I(SU)(C)
DS-2CD2326G2-I(U)(C)



Pro/2 Series with AcuSense	DS-2CD2326G2-ISU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2346G2-I(U)(C)
Pro/2 Series with	DS-2CD2346G2-ISU/SL(C)
AcuSense Pro/2 Series with	
AcuSense Pro/2 Series with	DS-2CD2366G2-I(U)(C)
AcuSense	DS-2CD2366G2-ISU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2386G2-I(U)(C)
Pro/2 Series with AcuSense	DS-2CD2386G2-ISU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2426G2-I(C)
Pro/2 Series with AcuSense	DS-2CD2446G2-I(C)
Pro/2 Series with AcuSense	DS-2CD2626G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2626G2-IZSU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2646G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2646G2-IZSU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2686G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2686G2-IZSU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2726G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2746G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2786G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2H26G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2H46G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2H86G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2T26G2-2I/4I(C)
Pro/2 Series with AcuSense	DS-2CD2T26G2-ISU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2T46G2-2I/4I(C)
L	



Pro/2 Series with AcuSense	DS-2CD2T46G2-ISU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2T66G2-2I/4I(C)
Pro/2 Series with	DS-2CD2T66G2-ISU/SL(C)
AcuSense Pro/2 Series with	DS-2CD2T86G2-2I/4I(C)
AcuSense Pro/2 Series with	DS-2CD2T86G2-ISU/SL(C)
AcuSense Pro/2 Series with	
ColorVu Pro/2 Series with	DS-2CD2027G2-L(U)(C)
ColorVu	DS-2CD2047G2-L(U)(C)
Pro/2 Series with ColorVu	DS-2CD2127G2(-(SU)(C)
Pro/2 Series with ColorVu	DS-2CD2147G2(-SU)(C)
Pro/2 Series with ColorVu	DS-2CD2327G2-L(U)(C)
Pro/2 Series with ColorVu	DS-2CD2347G2-L(U)(C)
Pro/2 Series with ColorVu	DS-2CD2647G2-LZS(C)
Pro/2 Series with ColorVu	DS-2CD2747G2-LZS(C)
Pro/2 Series with ColorVu	DS-2CD2T27G2-L(C)
Pro/2 Series with ColorVu	DS-2CD2T47G2-L(C)
Pro/3 Series with AcuSense	DS-2CD3026G2-IS(C)
Pro/3 Series with AcuSense	DS-2CD3026G2-IU/SL(C)
Pro/3 Series with AcuSense	DS-2CD3056G2-IS(C)
Pro/3 Series with AcuSense	DS-2CD3056G2-IU/SL(C)
Pro/3 Series with AcuSense	DS-2CD3086G2-IS(C)
Pro/3 Series with AcuSense	DS-2CD3126G2-IS(U)(C)
Pro/3 Series with AcuSense	DS-2CD3156G2-IS(U)(C)
Pro/3 Series with AcuSense	DS-2CD3186G2-IS(U)(C)
Pro/3 Series with AcuSense	DS-2CD3326G2-IS(U)(C)



Pro/3 Series with AcuSense	DS-2CD3326G2-ISU/SL(C)
Pro/3 Series with	
AcuSense	DS-2CD3356G2-IS(U)(C)
Pro/3 Series with	DC 3CD33E6C3 ICH/CI/C)
AcuSense	DS-2CD3356G2-ISU/SL(C)
Pro/3 Series with	DC 20D220C02 IS(0)
AcuSense	DS-2CD3386G2-IS(C)
Pro/3 Series with	
AcuSense	DS-2CD3626G2(T)-IZS(C)
Pro/3 Series with	
AcuSense	DS-2CD3656G2(T)-IZS(C)
Pro/3 Series with	DS-2CD3686G2(T)-IZS(C)
AcuSense	
Pro/3 Series with	DS-2CD3726G2(T)-IZS(C)
AcuSense	(, -\-1
Pro/3 Series with	DS-2CD3756G2(T)-IZS(C)
AcuSense	20 2000/0002(1/ 120(0)
Pro/3 Series with	DS 2CD2786G2/T) 175/C)
AcuSense	DS-2CD3786G2(T)-IZS(C)
Pro/3 Series with	DC 20D2D2C02T IZUCV(0)
AcuSense	DS-2CD3B26G2T-IZHSY(C)
Pro/3 Series with	
AcuSense	DS-2CD3B46G2T-IZHSY(C)
Pro/3 Series with	
AcuSense	DS-2CD3B86G2T-IZHSY(C)
Pro/3 Series with	
	DS-2CD3H26G2-IZS(C)
AcuSense	
Pro/3 Series with	DS-2CD3H56G2-IZS(C)
AcuSense	
Pro/3 Series with	DS-2CD3H86G2-IZS(C)
AcuSense	
Pro/3 Series with	DS-2CD3T26G2-4IS(C)
AcuSense	D3 20D312002 413(C)
Pro/3 Series with	DS 2CD2T26G2 ISH/SH/C\
AcuSense	DS-2CD3T26G2-ISU/SL(C)
Pro/3 Series with	DC 2002TFC02 410/0
AcuSense	DS-2CD3T56G2-4IS(C)
Pro/3 Series with	
AcuSense	DS-2CD3T56G2-ISU/SL(C)
Pro/3 Series with	
AcuSense	DS-2CD3T86G2-4IS(C)
Pro/3 Series with	
ColorVu	DS-2CD3047G2-LS(U)(C)
Pro/3 Series with	DS-2CD3347G2-LS(U)(C)
ColorVu	
Pro/3 Series with	DS-2CD3647G2-LZS(C)
ColorVu	



Pro/3 Series with	DS-2CD3747G2-LZS(C)	
ColorVu		

Note: Models in red font are newly released models.